



Made in the United States of America



The SCS Static Dissipative Kitting Trays are used to help organize an ESD protected workstation. They are made from a cleanable dissipative permanent PETG. The kitting trays are thermoformed for long term use and are inherently Static Dissipative. They are humidity insensitive and ultra clean, with low out-gassing and low ionic contamination. Ideal for medical device packaging, electronic component handling, hard disk packaging and more.

Properties	Typical Value	Test Method
Surface Resistance	≤ 10 <sup>9</sup>	ESD S11.11
Static Decay Rate (12% RH MD)	0.010 Sec	FTMS 101-C
Host Polymer	PETG	-----
Filler	IDP Alloy	-----
Color	Light Blue	Visual
Specific Gravity	1.25 g/cc	ASTM D-792
Tensile Modulus	160,000 psi	ASTM D-638
Tensile Strength (Break)	4,100 psi	ASTM D-638
Tensile Elongation (Break)	350%	ASTM D-638
Flexural Modulus	180,000 psi	ASTM D-790-92
Heat Deflection Temp @ 66 psi	140 °F	ASTM D-648
Heat Deflection Temp @ 264 psi	131 °F	ASTM D-648

Item No.	Size (Inches)	Cavity Size (Inches)	# of Cavities
<a href="#">770795</a>	10-1/2" x 8-5/8" x 1-1/2"	1-61/64" x 2-9/16" x 1-5/32"	12
<a href="#">770796</a>	14" x 10" x 1-3/4"	3-33/64" x 2-49/64" x 1-1/4"	9

Material starting gauge: ± 5%  
Thermoforming tolerance: ± .025  
Die cutting tolerance: ± .035  
Die cut registration: ± .063  
Tolerances for flatness and warp will vary with design.

Specifications and procedures subject to change without notice.

Note: Per Packaging standard ANSI/ESD S541 section 7.2.2 Resistance of Dissipative Materials "Packaging materials that are in intimate contact with devices should be dissipative."

### STATIC DISSIPATIVE KITTING TRAYS



926 JR Industrial Drive, Sanford, NC 27332  
WEB SITE: [StaticControl.com](http://StaticControl.com)  
PHONE (919) 718-0000

**DRAWING NUMBER**  
770795

**DATE:**  
March 2022